

Description

The 5100 Series Hall effect portable gaussmeters represent the most recent design from the world leader in magnetic measuring equipment. This new design incorporates the use of digital signal processing technology making it the world's first hand-held gaussmeter to have a digital signal processor (DSP) on board. F.W. Bell's exclusive Dynamic Probe Correction allows measurements from 0 to 30 kG with a basic accuracy of 1%.

Key features include Auto Zero, Min./Max./Peak Hold, Auto Range and Relative Mode. Both models allow the user to select Gauss, Tesla or Ampere/Meter readings. The 5180 features a corrected analog output (±3V FS) and a USB communication port.

The 5100 Series Hand-Held Gaussmeter's built-in software eliminates the need for complex calibration procedures. User prompts on the custom formatted LCD allow fast, simple push button operation. All models come equipped with a detachable transverse probe, zero gauss chamber, instruction manual, hard carrying case, and four AA batteries. Axial, ultra thin transverse and low-field probes are available as options.

Applications for the 5100 Series range from the most sensitive laboratory environment to the most rugged industrial setting. All instruments are CE compliant.

Features

	Model 5170	Model 5180
Probe Included	X	X
Auto Zero	X	X
Min/Max Hold	X	X
True RMS	X	X
Auto Range	X	X
True Peak Hold		X
Relative Mode		X
Outputs (analog)		X
USB Communication Port		X





5100 Series Specifications

Model	5170	5180	
Basic DC Accuracy	2%	1.1%	
Frequency Bandwidth	DC-20 kHz	DC-25 kHz	
Update Rates			
Display Analog Output	4 readings/sec None	4 readings/sec 100K samples/sec	
Ranges			
Ultra Low Range (low-field probe only) Low Range Mid Range High Range	1 G 200 G 2 kG 20 kG	1 G 300 G 3 kG 30 kG	
Resolution			
Ultra Low Range (low-field probe only) Low Range Mid Range High Range	1 mG 0.1 G 1.0 G 10 G	1 mG 0.1 G 1.0 G 10 G	
Display	LCD	LCD	
Digits	3 1/2	3 ² / ₃	
Readings	Gauss, Tesla, Amps/Meter	Gauss, Tesla, Amps/Meter	
Analog Output	None	±3V FS	
Communication Port	None	USB (1 samples/sec)	

General Information	All Models
Temperature Operating Storage	0°C to 50°C -25°C to 70°C
Power	4 AA batteries
Size	6.9 in x 3.9 in x 1.44 in.

Probes and Accessories

IONES	allu	ACCE	53501163	
Model N	umah au		Decerintie	

Model 5180 Probes

HTD18-0604 4" Transverse Probe

STD18-0404 4" Transverse Probe (incl. w/5180)

STD18-0402 2" Transverse Probe

SAD18-1904 4" Axial Probe

SAD18-1902 2" Axial Probe

Model 5170 Probes

HTH17-0604 4" Transverse Probe

STH17-0404 4" Transverse Probe (incl. w/5170)

STH17-0402 2" Transverse Probe

SAH17-1904 4" Axial Probe

SAH17-1902 2" Axial Probe

Models 5170/5180 Gaussmeter Probes

STB1X-0201 Ultra Thin Transverse Probe (0.020" thick)

MOS51-3204 Low Field Probe

Models 5170/5180 Gaussmeter Accessories

YA-111 Zero Gauss Chamber (for axial, transverse and low-field probes)

PSRD-5 AC Adapter, +5VDC Regulated Output, 110VAC Input, Domestic

PSRI-5 AC Adapter, +5VDC Regulated Output, 220VAC Input, Switching, International

Note: Due to continuous process improvement, specifications are subject to change without notice.





Shipping Weight

Domestic 3.5 lbs 1.59 kgs

International 4 lbs 1.82 kgs

SYPRIS 6120 Hanging Moss Road • Orlando, Florida 32807 • www.fwbell.com
Phone (407) 678-6900 • Fax (407) 677-5765 • Toll Free (800) 778-6117