Contact-Duo-Profile 3100.03101(F)

Functional description of the system

The evaluation electronics monitor the safety strip, which is equipped with a terminating resistor and operates using the closed circuit principle. An amount of current defined by the resistance (8.2 k Ω) flows through the safety strip. When mechanical pressure causes the resistance in the safety strip to drop below 5.5 k Ω , this is recognised as an actuation (evaluation electronics: LED RED). When contact resistance or a broken cable raises the resistance in the safety strip above 11.5 k Ω , this condition is recognised as a broken cable and/or fault (evaluation electronics: LED YELLOW). In both cases, the system stops (evaluation electronics: safety relays K1 and K2 open).



Contact-Duo 3100.0310I(F)

Contact-Duo-Profile	
Article no.	3100.0310I(F)
Material	EPDM
Weight	1.198 kg/m
Shore hardness	Conductive mixture: 65 +/-5 Shore A
	Non-conductive mixture: 60 +/-5 Shore A
Interconnection	Series connection electr. max. 10 switching strips
Min. and max. length of the	2 m to 100 m
switching strip	
Storage temperature	–10°C to +15°C respectively +25°C (DIN 7716)
Delivery length	20 m
Response time of the evaluation	< 12 ms
electronics	

Certified characteristic data	
Actuation force	87 N at 200 mm/s
Actuation angle (α)	+/-45°
Ineffective border area	0mm (left/right), 40mm (left/right)
	with finger safety
Finger safety	yes, in the range of 0°C upt to 55°C
Max. operating speed	200 mm/s, finger safety only up to 10 mm/s
Climatic conditions	−10°C to +55°C
Level of protection	IP67
Number of switching cycles	> 10,000 switching cycles

20°C
200 mm/s
87.0 N
9.6 mm
50 mm
31 mm*
36 mm*

For dimensions without tolerance particulars, tolerance-free dimensions as per DIN ISO 3302-1 E2 shall apply.

Certified characteristics and deformation travels refer to profile 3100.0310I. For profile 3100.0310IF, no significant difference can be seen.

You can choose any of several different variants for compatible evaluation signals (Category 1/PL c and Category 3/PL e, SIL3).



Profile cross-section Contact-Duo 3100.0310I(F)

st 1 mm reduction because of recovery